KERN **ADJ 200-4**



The price leader in analytical balances with internal adjustment



Category	
Brand	KERN
Product categoriy	Laboratory balance
Product group	Analytical balance
Product family	ADJ

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Force compensation
Weighing capacity [Max]	220 g
Weighing capacity [Max] (ct)	1100 ct
Readability [d]	0,0001 g
Readability carat [d] (ct)	0,0005 ct
Resolution	2.200.000
Linearity	± 0,0004 g
Reproducibility	0,0002 g
Default unit	g
Units	g ct lb oz
USP Minimum weight of sample (k = 2, U = 0.1%)	400 mg
Adjustment options	Internal calibration (automatic)
Recommended adjusting weight	200 g (E2)
Possible calibration points	100 g; 200 g
Automatic adjustment - Standard temperature deviation	2 °C
Automatic adjustment - Standard time interval	3 h
Stabilization time	3 s
Warm-up time	8 h

Eccentric loading at 1/3 [Max]	0,0005 g
Maximum creep (15 minutes)	1 mg
Maximum creep (30 minutes)	2 mg

Approval	
CE mark	✓

Display	
Display type	LCD
Display type	7 segment LED
Display backlight	✓
Display digit height - smallest digit	16 mm
Display digit height	16 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	230×310×330 mm
Dimensions rectangular draught shield - inner (W×D×H)	170×160×205 mm
Dimensions rectangular draught shield - outer (W×D×H)	175×175×230 mm
Material display housing	Plastics
Material housing	cast aluminium, plastic
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	90 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Standby function	✓
Interfaces	RS-232 standard

Counting	
Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Reference quantity	5, 10, 20, 50, 100
Counting resolution (laboratory conditions)	220.000

1

KERN **ADJ 200-4**



The price leader in analytical balances with internal adjustment

Power Supply	
Input voltage power supply / power [Max]	100 - 265 V; 50 - 60 Hz; 2,0 A
Input voltage device / power [Max]	12 V; 2 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US

Environmental conditions	
Humity of environment [Min]	20 %
Humity of environment [Max]	85 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	325×443×396 mm
Net weight	5 kg
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	8 kg
Shipping weight	11,4 kg

Services (optional)	
Article number for DAkkS calibration	963-101
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

