KERN CCS 300K0.01



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Counting system
Product family	CCS
Measuring System	
Reference scale - item number	CFS 3K-5
Quantity scale - Item number	KFP 300V20M
Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Reference scale - Weighing capacity [Max]	3 kg
Quantity scale - Weighing capacity [Max]	300 kg
Reference scale - Readability [d]	10 mg
Quantity scale - Readability [d]	0,01 kg
Linearity	±
Reference scale - Linearity	100 mg
Quantity scale - Linearity	0,04 kg
Reproducibility	0,00002 kg
Reference scale - Reproducibility	30 mg
Quantity scale - Reproducibility	0,01 kg
Default unit	kg
Units	kg Ib
Adjustment options	Adjusting with external weight
Recommended adjusting weight	300 kg (M1)
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,00005 kg
Reference scale - Eccentric loading at 1/3 [Max]	60 mg
Quantity scale - Eccentric loading at 1/3 [Max]	0,05 kg
Loadcell type	HBM PW6KRC3

Approval	<i>.</i>
CE mark	√
Display	
Display type	LCD
Display backlight	✓
Display digit height	20 mm
Construction	
Dimensions weighing platform (W×D×H)	650×500×136 mm
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	650×500 mm
Cable length	1,5 m
Display device cable length	2,5 m
Levelling feet adjustable	\checkmark
Functions	
Number of keys for operation	20
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
PreTare function	1
Tare function	manual (multi)
Counting function	1
Tolerance weighing	\checkmark
Tolerance weighing - type of signal	acoustically visual
Conversion function	\checkmark
Recipe/summing level	Sum A
PLU - total	100
Sum memory function	1
Memory function	
Underfloor weighing	None
Interfaces	RS-232 standard
IP protection - display IP protection - load cell	IP23 IP65
IP protection - platform	IP65
Counting	
Smallest piece weight when piece counting - laboratory conditions	50 mg
Smallest piece weight when piece counting - normal conditions	500 mg
Counting reference weight can be	1

KERN CCS 300K0.01



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999

Reference quantity	n (any number of pieces)
Counting resolution (laboratory conditions)	6.000.000
Power Supply	
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	70 h
Rechargeable battery operating time - backlight off	60 h
Environmental conditions	
Humity of environment [Min]	0 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C

Article number for DAkkS calibration	962-129-127
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



3 DAYS

OPTION

DAkkS
+3 DAYS

Packing & Shipping Readability force [d] (N)

Storage temperature [Min]

Storage temperature [Max]

3 d
670×1045×545 mm
23,7 kg
Parcel service
24 kg
30 kg
76,3 kg

-20 °C

60 °C

Services (optional)

Article number for adjustment at the location of installation

abhängig von Auflösung/ Max | depends on resolution and capacity