KERN CDS 60K0.2



Easy to use industrial counting scale for heavy loads, counting resolution 300.000 points, ideal for the diverse possibilities of Industry 4.0 applications



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Counting scale
Product family	CDS

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	60 kg
Readability [d]	0,0002 kg
Resolution	300.000
Linearity	± 0,0006 kg
Reproducibility	0,0004 kg
Default unit	kg
Units	kg g dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (F1)
Possible calibration points	20 kg; 30 kg; 50 kg; 60 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,001 kg
Maximum creep (15 minutes)	2 g

Maximum creep (30 minutes)	4 g
Approval	
CE mark	✓
Display	
Display type	LCD
Display type	7 segment LED
Display screen size	89×30 mm
Display backlight	✓
Display digit height	21 mm
Languages of the user interface	English Symbol language
Construction	
Dimension display device (W×D×H)	225×115×60 mm
Dimension housing (W×D×H)	225×115×60 mm
Dimensions weighing platform (W×D×H)	500×400×125 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material platform	metal, lacquered
Dimensions weighing surface (W×D)	500×400 mm
Display device cable length	0,6 m
Transport safety lock - bolt torque	0,1 Nm
Levelling feet adjustable	✓
Wall mount	✓
Functions	
Number of keys for operation	7
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 2 min 1 min 30 min 60 min 30 sec
PreTare function	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically

visual

1

KERN CDS 60K0.2



Easy to use industrial counting scale for heavy loads, counting resolution 300.000 points, ideal for the diverse possibilities of Industry 4.0 applications

Function for averaging under unstable weighing conditions	✓
Underfloor weighing	None
Interfaces	RS-232 (optional) Ethernet (optional) Bluetooth BLE (v4.0) (optional) USB-Device (optional) KUP WiFi (optional)

200 mg
2 g
/
5, 10, 20, 50, n (any number of pieces)
300.000
2

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h

80 %

-10 °C

40 °C

Environmental conditions Humity of environment [Max]

Ambient temperature [Min]

Ambient temperature [Max]

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	600×510×230 mm
Net weight	19 kg
Shipping method	Parcel service
Net weight approx.	19 kg
Gross weight approx.	22 kg
Shipping weight	20,5 kg

Services (optional)	
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD

















OPTION













