KERN CCA 100K-5M



High-resolution counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999, verification optional



| Category | |
|-------------------|------------------|
| Brand | KERN |
| Product categoriy | Industrial scale |
| Product group | Counting system |
| Product family | CCA |

| Measuring System | |
|--|--------------------------------|
| Reference scale - item number | EWJ 600-2M |
| Quantity scale - Item number | IFS 100K-2M |
| Conformity assessment possible | ✓ |
| Weighing system | Strain gauge |
| Reference scale - Weighing capacity [Max] | 0,6 kg |
| Quantity scale - Weighing capacity [Max] | 60 kg; 150 kg |
| Reference scale - Readability [d] | 10 mg |
| Quantity scale - Readability [d] | 0,02 kg; 0,05 kg |
| Linearity | ± |
| Reference scale - Linearity | 30 mg |
| Quantity scale - Linearity | 0,02 kg; 0,05 kg |
| Reference scale - Reproducibility | 10 mg |
| Quantity scale - Reproducibility | 0,02 kg; 0,05 kg |
| Default unit | kg |
| Units | kg |
| Units (if device is conformity assessed) | kg |
| Adjustment options | Adjusting with external weight |
| Recommended adjusting weight | 6 kg (M1) |
| Stabilization time | 2 s |
| Reference scale - Eccentric loading at 1/3 [Max] | 30 mg |
| Quantity scale - Eccentric loading at 1/3 [Max] | 0,02 kg; 0,05 kg |

Approval
CE mark

| Pattern approval for conformity assessment | ✓ |
|--|---|
| Conformity assessment possible ex works | ✓ |

| Display | |
|----------------------|-------|
| Display type | LCD |
| Display backlight | ✓ |
| Display digit height | 20 mm |

| Construction | |
|--------------------------------------|----------------|
| Dimensions weighing platform (W×D×H) | 500×400×140 mm |
| Material housing | plastic |
| Material weighing plate | coated metal |
| Dimensions weighing surface (W×D) | 500×400 mm |
| Cable length | 1,5 m |
| Display device cable length | 5 m |
| Material load cell(s) | aluminium |
| Levelling feet adjustable | ✓ |

| Functions | |
|-------------------------------------|------------------------|
| Number of keys for operation | 28 |
| PreTare function | ✓ |
| Tare function | manual (multi) |
| Counting function | ✓ |
| Tolerance weighing | ✓ |
| Tolerance weighing - type of signal | acoustically visual |
| Conversion function | ✓ |
| Recipe/summing level | Rez A (Net total) |
| PLU - total | 100 |
| Sum memory function | ✓ |
| Memory function | ✓ |
| Interfaces | RS-232 standard |
| IP protection - complete device | IP23 |
| IP protection - load cell | IP65 |
| IP protection - platform | IP65 |

| Counting | |
|---|--------------------|
| Smallest piece weight when piece counting - laboratory conditions | 20 mg |
| Smallest piece weight when piece counting - normal conditions | 200 mg |
| Counting reference weight can be entered | 1 |
| Reference quantity | 5, 10, 20, 50, 100 |

1

KERN CCA 100K-5M



High-resolution counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999, verification optional

Counting resolution (laboratory conditions)

time - backlight on

time - backlight off

Battery connection

Rechargeable battery operating

Battery / accumulator type

7.500.000

| Power Supply | |
|---|-------------------------------|
| Input voltage power supply / power [Max] | 100 - 240 V |
| Input voltage device / power [Max] | 12 V, 500 mA |
| Plug-in power supply type | Power adapter |
| Supplied power supply | Power supply unit |
| Plug-in power supply / adapter for countries - included with the delivery | EURO UK US CH |
| Plug-in power supply / adapter for countries - optional | EURO AUS UK US CH |
| Rechargeable battery charging time | 12 h |
| Rechargeable battery operating | 8 h |

8 h

18 h

Plug-in terminals

Pb

| Environmental conditions | |
|-----------------------------|--------|
| Humity of environment [Min] | 0 % |
| Humity of environment [Max] | 80 % |
| Ambient temperature [Min] | 0 °C |
| Ambient temperature [Max] | 40 °C |
| Storage temperature [Min] | -20 °C |
| Storage temperature [Max] | 60 °C |

| Packing & Shipping | |
|------------------------------|----------------|
| Readability force [d] (N) | 4 d |
| Dimensions packaging (W×D×H) | 930×545×485 mm |
| Net weight | 15,1 kg |
| Shipping method | Parcel service |
| Net weight approx. | 16 kg |
| Gross weight approx. | 18 kg |
| Shipping weight | 49,2 kg |

| Services (optional) | |
|--|-------------|
| Article number for conformity assessment | 965-229-216 |
| Article number for DAkkS calibration | 962-129-127 |

Article number for certificate of 969-517 conformity (verification)

Pictograms

STANDARD



OPTION



FACTORY

