

# KERN CK 2-0P1

Miniature load cell made of aluminium

# KERN



## Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CK P1

## Measuring System

Weighing capacity [Max]	2 kg
Load cell connection	4-wire
Load cell OIML class	C2
Load cell - characteristic value - nominal	1,2 mV/V
Load cell - characteristic value - variance	0,15 mV/V
Load cell - Combined error	0,03%
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Load cell - Input resistance - nominal	1055 $\Omega$
Load cell - Output resistance - nominal	1000 $\Omega$
Load cell - Isolation resistance - [Min]	2000 M $\Omega$
Load cell - Recommended excitation voltage [Min]	5 V
Load cell - Recommended excitation voltage [Max]	9 V
Load cell - Input resistance - variance	10 $\Omega$
Load cell - Output resistance - variance	10 $\Omega$
Directions of force	compression

## Approval

CE mark	✓
---------	---

## Construction

Design	Miniature bending beam
Dimension (W×D×H)	80×10×12,7 mm
Material	aluminium
Cable length	0,25 m
Mounting - force application	2 × threaded hole M4
Mounting - force dissipation	2 × threaded hole M5

## Functions

IP protection - complete device	IP65
---------------------------------	------

## Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	65 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	145×60×35 mm
Net weight	0,012 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

## Services (optional)

Article number for DAkkS calibration (compressive force)	963-261V
--	----------

## Pictograms

### STANDARD



### OPTION

