KERN CCS 10K-6



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Counting system
Product family	CCS
Measuring System	
Reference scale - item number	CFS 300-3
Quantity scale - Item number	KFP 15V20M
Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Reference scale - Weighing capacity [Max]	0,3 kg
Quantity scale - Weighing capacity [Max]	15 kg
Reference scale - Readability [d]	1 mg
Quantity scale - Readability [d]	0,0005 kg
Linearity	±
Reference scale - Linearity	4 mg
Quantity scale - Linearity	0,0015 kg
Reproducibility	0,000002 kg
Reference scale - Reproducibility	2 mg
Quantity scale - Reproducibility	0,0005 kg
Default unit	kg
Units	g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (F1)
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,000006 kg
Reference scale - Eccentric loading at 1/3 [Max]	6 mg
Quantity scale - Eccentric loading at 1/3 [Max]	0,0025 kg
Loadcell type	aluminum Alloy IP64

Approval	
CE mark	1
Display	
Display type	LCD
Display backlight	J
Display digit height	20 mm
Construction	
Dimensions weighing platform (W×D×H)	300×240×105 mm
Dimensions completely mounted (W×D×H)	320×330×125 mm
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	300×240 mm
Cable length	1,5 m
Display device cable length	2,5 m
Material load cell(s)	aluminium
Levelling feet adjustable	1
Functions	
Auto-off interval(s) in mains power mode	5 min 30 min 15 min
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
PreTare function	\checkmark
Tare function	manual (multi)
Counting function	\checkmark
Tolerance weighing	\checkmark
Conversion function	1
	•
Recipe/summing level	Sum A
· ·	-
PLU - total	Sum A
PLU - total Sum memory function	Sum A 100
Sum memory function Memory function Interfaces	Sum A 100 ✓
PLU - total Sum memory function Memory function Interfaces	Sum A 100 ✓
PLU - total Sum memory function Memory function	Sum A 100 ✓ ✓ RS-232 standard
PLU - total Sum memory function Memory function Interfaces IP protection - display IP protection - load cell	Sum A 100 ✓ ✓ RS-232 standard IP23
PLU - total Sum memory function Memory function Interfaces IP protection - display IP protection - load cell	Sum A 100 ✓ ✓ RS-232 standard IP23 IP65
PLU - total Sum memory function Memory function Interfaces IP protection - display IP protection - load cell IP protection - platform	Sum A 100 ✓ ✓ RS-232 standard IP23 IP65

KERN CCS 10K-6



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999

Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)
Counting resolution (laboratory conditions)	3.000.000
Power Supply	
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	40 h
Rechargeable battery operating time - backlight off	60 h
Battery / accumulator type	Pb
Environmental conditions	
Humity of environment [Min]	0 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	0 ° C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C
Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	630×535×350 mm
Net weight	6,9 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	10 kg
Shipping weight	23,6 kg

Services (optional)	
Article number for adjustment at the location of installation	abhängig von Auflösung/ Max depends on resolution and capacity
Article number for DAkkS calibration	962-128-127
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



2 DAYS

OPTION

	DAkkS
ACCU	+3 DAYS