KERN CCS 30K0.01.



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Counting system
Product family	CCS

Measuring System	
Reference scale - item number	CFS 3K-5
Quantity scale - Item number	TKFP 30V20M-A
Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Reference scale - Weighing capacity [Max]	3 kg
Quantity scale - Weighing capacity [Max]	30 kg
Reference scale - Readability [d]	10 mg
Quantity scale - Readability [d]	1 g
Linearity	±
Reference scale - Linearity	100 mg
Quantity scale - Linearity	4 g
Reproducibility	20 mg
Reference scale - Reproducibility	30 mg
Quantity scale - Reproducibility	1 g
Default unit	kg
Units	kg Ib
Adjustment options	Adjusting with external weight
Recommended adjusting weight	30 kg (M1)
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	50 mg
Reference scale - Eccentric loading at 1/3 [Max]	60 mg
Quantity scale - Eccentric loading at 1/3 [Max]	5 g
Loadcell type	HBM PW6KRC3

Approval	
CE mark	✓
Display	
Display type	LCD
Display backlight	✓
Display digit height	20 mm
Construction	
Dimensions weighing platform (W×D×H)	400×300×114 mm
Dimensions completely mounted (W×D×H)	320×330×125 mm

Material housing
Material weighing plate

(W×D)

Cable length

Counting

Smallest piece weight when piece

counting - laboratory conditions Smallest piece weight when piece

counting - normal conditions

Dimensions weighing surface

Display device cable length

plastic

1,5 m

2,5 m

stainless steel

400×300 mm

Levelling feet adjustable	1
Functions	
Number of keys for operation	20
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
PreTare function	✓
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Conversion function	✓
Recipe/summing level	Sum A
PLU - total	100
Sum memory function	✓
Memory function	✓
Underfloor weighing	None
Interfaces	RS-232 standard
IP protection - display	IP23
IP protection - load cell	IP65
IP protection - platform	IP65

50 mg

KERN CCS 30K0.01.



⊙ 3%

MULTI

Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999

Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)
Counting resolution (laboratory conditions)	600.000

Power Supply	
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	70 h
Rechargeable battery operating time - backlight off	60 h

Environmental conditions	
Humity of environment [Min]	0 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

2 d
940×640×230 mm
12,05 kg
Parcel service
13 kg
16 kg
27,7 kg

Services (optional)	
Article number for adjustment at the location of installation	abhängig von Auflösung/ Max depends on resolution and capacity
Article number for DAkkS calibration	962-128-127
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD





OPTION

