

KERN CKE 6K0.02



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution 300.000 points



Approval

CE mark ✓

Display

Display type LCD
 Display screen size 120×38 mm
 Display backlight ✓
 Display digit height 25 mm

Construction

Dimension housing (W×D×H) 350×390×120 mm
 Dimensions weighing platform (W×D×H) 340×240×21 mm
 Material display housing Plastics
 Material housing ABS plastic
 Material weighing plate stainless steel
 Dimensions weighing surface (W×D) 340×240 mm
 Levelling feet adjustable ✓

Functions

Number of keys for operation 7
 Auto-off interval(s) in mains power mode 5 min
 2 min
 1 min
 30 min
 Auto-off interval(s) in battery mode/rechargeable battery mode 5 min
 2 min
 1 min
 30 min
 60 min
 30 sec
 PreTare function ✓
 Tare function manual (multi)

Counting function ✓
 Tolerance weighing ✓

Tolerance weighing - type of signal acoustically
 visual

Underfloor weighing Hook (included in delivery)

Interfaces RS-232 (optional)
 Ethernet (optional)
 Bluetooth BLE (v4.0) (optional)
 USB-Device (optional)
 KUP
 WiFi (optional)

Category

Brand KERN
 Product category Industrial scale
 Product group Counting scale
 Product family CKE

Measuring System

Construction type of the scale Single-range balance
 Weighing system Strain gauge
 Weighing capacity [Max] 6000 g
 Readability [d] 0,02 g
 Resolution 300.000
 Linearity ± 0,2 g
 Reproducibility 0,04 g
 Default unit g

Units kg
 g
 gn
 dwt
 ozt
 lb
 oz
 ffa
 PCS

Adjustment options Adjusting with external weight

Recommended adjusting weight 6 kg (F1)
 Possible calibration points 2 kg; 4 kg; 6 kg
 Stabilization time 3 s
 Warm-up time 120 min
 Eccentric loading at 1/3 [Max] 0,2 g
 Maximum creep (15 minutes) 200 mg
 Maximum creep (30 minutes) 400 mg

KERN CKE 6K0.02



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution 300.000 points

Counting

Smallest piece weight when piece counting - laboratory conditions	20 mg
Smallest piece weight when piece counting - normal conditions	200 mg
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	300.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Battery	4×1.5 V AA
Battery / accumulator type	Li-Ion
Battery connection	Battery insert
Battery operating time	20 h

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	470×470×190 mm
Net weight	6,5 kg
Shipping method	Parcel service

Net weight approx.	7 kg
Gross weight approx.	8 kg
Shipping weight	8,4 kg

Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

