

KERN CCS 6K-6



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999



Category

Brand	KERN
Product category	Industrial scale
Product group	Counting system
Product family	CCS

Measuring System

Reference scale - item number	CFS 300-3
Quantity scale - Item number	TKFP 6V20M-A
Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Reference scale - Weighing capacity [Max]	0,3 kg
Quantity scale - Weighing capacity [Max]	6 kg
Reference scale - Readability [d]	1 mg
Quantity scale - Readability [d]	0,0002 kg
Linearity	±
Reference scale - Linearity	4 mg
Quantity scale - Linearity	0,0006 kg
Reproducibility	0,000002 kg
Reference scale - Reproducibility	2 mg
Quantity scale - Reproducibility	0,0002 kg
Default unit	kg
Units	g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6 kg (F1)
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,000006 kg
Reference scale - Eccentric loading at 1/3 [Max]	6 mg
Quantity scale - Eccentric loading at 1/3 [Max]	0,001 kg
Loadcell type	aluminum Alloy IP64

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display backlight	✓
Display digit height	20 mm

Construction

Dimensions weighing platform (W×D×H)	230×230×103 mm
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	230×230 mm
Cable length	1,5 m
Display device cable length	2,5 m
Material load cell(s)	aluminium
Levelling feet adjustable	✓

Functions

Number of keys for operation	20
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
PreTare function	✓
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Conversion function	✓
Recipe/summing level	Sum A
PLU - total	100
Sum memory function	✓
Memory function	✓
Interfaces	RS-232 standard
IP protection - display	IP23
IP protection - load cell	IP65
IP protection - platform	IP65

Counting

Smallest piece weight when piece counting - laboratory conditions	5 mg
Smallest piece weight when piece counting - normal conditions	50 mg
Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)

KERN CCS 6K-6



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999

Counting resolution (laboratory conditions)	1.200.000
---	-----------

Article number for certificate of conformity (verification)	969-517
---	---------

Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
--	-------------------------

Input voltage device / power [Max]	12 V, 500 mA
------------------------------------	--------------

Plug-in power supply type	Power adapter
---------------------------	---------------

Supplied power supply	Power supply unit
-----------------------	-------------------

Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
---	------------------------

Plug-in power supply / adapter for countries - optional	EURO UK US CH
---	------------------------

Rechargeable battery optional	Rchrg. battery optional
-------------------------------	-------------------------

Rechargeable battery charging time	12 h
------------------------------------	------

Rechargeable battery operating time - backlight on	40 h
--	------

Rechargeable battery operating time - backlight off	60 h
---	------

Battery / accumulator type	Pb
----------------------------	----

Environmental conditions

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

Ambient temperature [Min]	0 °C
---------------------------	------

Ambient temperature [Max]	40 °C
---------------------------	-------

Storage temperature [Min]	-20 °C
---------------------------	--------

Storage temperature [Max]	60 °C
---------------------------	-------

Packing & Shipping

Readability force [d] (N)	2 d
---------------------------	-----

Dimensions packaging (W×D×H)	630×535×350 mm
------------------------------	----------------

Net weight	6,21 kg
------------	---------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	7 kg
--------------------	------

Gross weight approx.	10 kg
----------------------	-------

Shipping weight	23,6 kg
-----------------	---------

Services (optional)

Article number for adjustment at the location of installation	abhängig von Auflösung/ Max depends on resolution and capacity
---	--

Article number for DAkkS calibration	962-128-127
--------------------------------------	-------------

Pictograms

STANDARD



OPTION

