


# KERN CE HSA



Compact display device (rail-mounted module) for installation in switch cabinets



IP protection - complete device IP20

## Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	70 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	260×155×140 mm
Net weight	0,149 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,45 kg
Shipping weight	1,1 kg

## Services (optional)

Article number for adjustment at the location of installation	auf Anfrage   on request
---	--------------------------

## Pictograms

### STANDARD



## Category

Brand	Sauter
Product category	Measuring Technology Component
Product group	Digital weighing transmitter
Product family	CE HS

## Measuring System

Terminal resolution (not verifiable)	10.000
Adjustment options	Adjusting with external weight
Load cell connection	6-wire
Number of platforms / channels	1
Internal measuring frequency	1600 Hz

## Approval

CE mark	✓
---------	---

## Display

Display type	7 segment LED
Display digit height	7,62 mm

## Construction

Dimension display device (W×D×H)	120×101×23 mm
----------------------------------	---------------

## Functions

Number of keys for operation	3
Tare function	automatic & manual (multi)
Interfaces	RS-485 analogue (4 - 20 mA) USB-Device