


KERN CE HSP



Compact display device (rail-mounted module) for installation in switch cabinets



IP protection - complete device IP20

Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	70 °C

Packing & Shipping


Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	260×155×140 mm
Net weight	0,149 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,45 kg
Shipping weight	1,1 kg

Services (optional)

Article number for adjustment at the location of installation	auf Anfrage on request
---	--------------------------

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Measuring Technology Component
Product group	Digital weighing transmitter
Product family	CE HS

Measuring System

Terminal resolution (not verifiable)	10.000
Adjustment options	Adjusting with external weight
Load cell connection	6-wire
Number of platforms / channels	1
Internal measuring frequency	1600 Hz

Approval

CE mark	✓
---------	---

Display

Display type	7 segment LED
Display digit height	7,62 mm

Construction

Dimension display device (W×D×H)	120×101×23 mm
----------------------------------	---------------

Functions

Number of keys for operation	3
Tare function	automatic & manual (multi)
Interfaces	Digital I/O RS-485 USB-Device Profibus DP over EIA-485