

KERN CK 300-OP4

Miniature load cell made of aluminium

KERN



Category

| | |
|------------------|----------------|
| Brand | Sauter |
| Product category | Measuring cell |
| Product group | Load cell |
| Product family | CK P4 |

Measuring System

| | |
|--|-------------|
| Weighing capacity [Max] | 300 g |
| Load cell connection | 4-wire |
| Load cell OIML class | C1 |
| Load cell - characteristic value - nominal | 0,9 mV/V |
| Load cell - characteristic value - variance | 0,18 mV/V |
| Load cell - Combined error | 0,05% |
| Load cell - Dead load [Min] (%) | 0% |
| Measuring applications | mass |
| Load cell - Input resistance - nominal | 1055 Ω |
| Load cell - Output resistance - nominal | 1000 Ω |
| Load cell - Isolation resistance - [Min] | 2000 MΩ |
| Load cell - Recommended excitation voltage [Min] | 2 V |
| Load cell - Recommended excitation voltage [Max] | 5 V |
| Load cell - Input resistance - variance | 10 Ω |
| Load cell - Output resistance - variance | 10 Ω |
| Directions of force | compression |

Approval

| | |
|---------|---|
| CE mark | ✓ |
|---------|---|

Construction

| | |
|------------------------------|------------------------|
| Design | Miniature bending beam |
| Dimension (W×D×H) | 47×20×6,6 mm |
| Material | aluminium |
| Cable length | 0,25 m |
| Mounting - force dissipation | 2 × threaded hole M3 |

Functions

| | |
|---------------------------------|------|
| IP protection - complete device | IP65 |
|---------------------------------|------|

Environmental conditions

| | |
|---------------------------|--------|
| Use temperature [Min] | -10 °C |
| Use temperature [Max] | 40 °C |
| Ambient temperature [Min] | -10 °C |
| Ambient temperature [Max] | 40 °C |
| Storage temperature [Min] | -20 °C |
| Storage temperature [Max] | 65 °C |

Packing & Shipping

| | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 145×60×35 mm |
| Net weight | 0,01 kg |
| Shipping method | Parcel service |
| Net weight approx. | 0,05 kg |
| Gross weight approx. | 0,40 kg |
| Shipping weight | 0,37 kg |

Services (optional)

| | |
|--|----------|
| Article number for DAkkS calibration (compressive force) | 963-261V |
|--|----------|

Pictograms

STANDARD



OPTION

