KERN CKE 36K0.1



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution 360.000 points



Category				
Brand	KERN			
Product categoriy	Industrial scale			
Product group	Counting scale			
Product family	CKE			
Measuring System				
Construction type of the scale	Single-range balance			
Weighing system	Strain gauge			
Weighing capacity [Max]	36 kg			
Readability [d]	0,0001 kg			
Resolution	360.000			
Linearity	± 0,0005 kg			
Reproducibility	0,0002 kg			
Default unit	kg			
Units	kg g gn dwt ozt lb oz ffa PCS			
Adjustment options	Adjusting with external weight			
Recommended adjusting weight	30 kg (E2)			
Possible calibration points	10 kg; 20 kg; 30 kg			
Stabilization time	3 s			
Warm-up time	120 min			
Eccentric loading at 1/3 [Max]	0,001 kg			
Maximum creep (15 minutes)	1 g			
Maximum creep (30 minutes)	2 g			

Approval				
CE mark	1			
Display				
Display type	LCD			
Display screen size	120×38 mm			
Display backlight	✓ 05			
Display digit height	25 mm			
Construction				
Dimension housing (W×D×H)	350×390×120 mm			
Dimensions weighing platform (W×D×H)	340×240×21 mm			
Material display housing	Plastics			
Material housing	ABS plastic			
Material weighing plate	stainless steel			
Dimensions weighing surface (W×D)	340×240 mm			
Levelling feet adjustable	1			
Functions				
Number of keys for operation	7			
Auto-off interval(s) in mains power mode	5 min 2 min 1 min 30 min			
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 2 min 1 min 30 min 60 min 30 sec			
PreTare function	✓			
Tare function	manual (multi)			
Counting function	\checkmark			
Tolerance weighing	1			
Tolerance weighing - type of signal	acoustically visual			
Underfloor weighing	Hook (included in delivery)			
Interfaces	RS-232 (optional) Ethernet (optional) Bluetooth BLE (v4.0) (optional) USB-Device (optional) KUP WiFi (optional)			

KERN CKE 36K0.1



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution 360.000 points

Counting

Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Counting reference weight can be entered	1
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	360.000

Power Supply

	Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz			
	Input voltage device / power [Max]	5,9V, 1A			
	Plug-in power supply type	Power adapter			
	Supplied power supply	Power supply unit			
	Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH			
	Plug-in power supply / adapter for countries - optional	EURO UK US CH			
	Rechargeable battery optional	Rchrg. battery optional - intern			
	Rechargeable battery charging time	8 h			
	Rechargeable battery operating time - backlight on	24 h			
	Rechargeable battery operating time - backlight off	48 h			
	Battery	4×1.5 V AA			
	Battery / accumulator type	Li-Ion			
	Battery connection	Battery insert			
	Battery operating time	20 h			
	Environmental conditions				
	Humity of environment [Max]	80 %			

Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d		
Dimensions packaging (W×D×H)	470×470×190 mm		
Net weight	6,5 kg		
Shipping method	Parcel service		

Net weight approx.	7 kg
Gross weight approx.	8 kg
Shipping weight	8,4 kg

Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



DMS 1 DAY

OPTION

1	• 4882. •	€ →	(((-	الل	- - -		DAkkS
ET	RS 232	USB	WLAN	BT 4.0	LAN	ACCU	+3 DAYS