


KERN CP 50-3P9

Single-point load cell made from stainless steel

KERN



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CP P9

Measuring System

Weighing capacity [Max]	50 kg
Load cell connection	6-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Maximum platform size	400×400 mm
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	0,2 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,023%
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Load cell - Input resistance - nominal	380 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Recommended excitation voltage [Min]	5 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Input resistance - variance	15 Ω
Load cell - Output resistance - variance	10 Ω
Directions of force	compression

Approval

CE mark	✓
Pattern approval for conformity assessment	✓

Construction

Design	Singlepoint load cell
Dimension (W×D×H)	150×40×25 mm
Material	stainless steel
Cable length	3 m
Mounting - force application	Threaded hole M6
Mounting - force dissipation	Threaded hole M6

Functions

IP protection - complete device	IP68 IP69K
---------------------------------	---------------

Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Ambient temperature [Min]	-35 °C
Ambient temperature [Max]	65 °C
Storage temperature [Min]	-40 °C
Storage temperature [Max]	70 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	230×115×45 mm
Net weight	0,997 kg
Shipping method	Parcel service
Net weight approx.	1,00 kg
Gross weight approx.	1,2 kg
Shipping weight	1,075 kg

Services (optional)

Article number for DAkKS calibration (compressive force)	963-261V
----------------------------------------------------------	----------

KERN CP 50-3P9

Single-point load cell made from stainless steel



Pictograms

STANDARD



OPTION

