

KERN CS 2000-3P1

KERN

4-wire "S" measuring cell made of nickel-plated steel for force and mass measurement



Category	
Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CS P1

Measuring System	
Weighing capacity [Max]	2000 kg
Load cell connection	4-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,02%
Measuring applications	force mass
Load cell - Input resistance - nominal	350 Ω
Load cell - Output resistance - nominal	351 Ω
Load cell - Isolation resistance - [Min]	500 MΩ
Measuring range force [Max] (N)	20 kN
Directions of force	tension compression

Approval	
CE mark	✓
Construction	
Design	"S" shaped cell

Dimension (W×D×H)	76,2×101,6×27,2 mm
Material	steel, nickel-plated
Cable length	6 m
Mounting - force application	Threaded hole M20 × 1,5
Mounting - force dissipation	Threaded hole M20 × 1,5

Functions	
IP protection - complete device	IP67

Environmental conditions	
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Ambient temperature [Min]	-35 °C
Ambient temperature [Max]	65 °C
Storage temperature [Min]	-40 °C
Storage temperature [Max]	70 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	200×170×60 mm
Net weight	1,3 kg
Shipping method	Parcel service
Net weight approx.	1,4 kg
Gross weight approx.	1,6 kg
Shipping weight	1,41 kg

Services (optional)	
Article number for factory calibration (tensile force)	961-164V
Article number for factory calibration (tensile force/compressive force)	961-364V

Pictograms	
------------	--

STANDARD	
----------	--



IP 67
1 DAY

OPTION	
--------	--

