KERN CS 1000-3P1



4-wire "S" measuring cell made of nickel-plated steel for force and mass measurement



Category	
Brand	Sauter
Product categoriy	Measuring cell
Product group	Load/force measuring cell
Product family	CS P1

Measuring System	
Weighing capacity [Max]	1000 kg
Load cell connection	4-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	0,004 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,02%
Load cell - Dead load [Min] (%)	0%
Measuring applications	force mass
Load sell - Input resistance - nominal	350 Ω
Load cell - Output resistance - nominal	351 Ω
Load cell - Isolation resistance - [Min]	500 ΜΩ
Load cell - Recommended exitation voltage [Min]	5 V
Load cell - Recommended exitation voltage [Max]	12 V
Load cell - Input resistance - variance	3,5 Ω

Load cell - Output resistance - variance	2 Ω
Measuring range force [Max] (N)	10 kN
Directions of force	tension compression

Approval

CE mark	✓
Construction	
Design	"S" shaped cell
Dimension (W×D×H)	50,8×76,2×27,2 mm
Material	steel, nickel-plated
Cable length	3 m
Mounting - force application	Threaded hole M12
Mounting - force dissipation	Threaded hole M12
Functions	
IP protection - complete device	IP67

Environmental conditions	
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Ambient temperature [Min]	-35 °C
Ambient temperature [Max]	65 °C
Storage temperature [Min]	-40 °C
Storage temperature [Max]	70 °C

1 d
185×155×60 mm
0,658 kg
Parcel service
0,70 kg
0,80 kg
0,76 kg

Services (optional)	
Article number for factory calibration (tensile force)	961-164V
Article number for factory calibration (tensile force/compressive force)	961-364V

1

KERN CS 1000-3P1



4-wire "S" measuring cell made of nickel-plated steel for force and mass measurement

Pictograms

STANDARD





OPTION

