KERN CS 5-Y1



Miniature "S"-load/force measuring cell made of stainless steel



Category	
Brand	Sauter
Product categoriy	Measuring cell
Product group	Load/force measuring cell
Product family	CS Y1

Measuring System	
Weighing capacity [Max]	5 kg
Load cell connection	4-wire
Load cell - characteristic value - nominal	2 mV/V
Load cell - Combined error	0,05%
Measuring applications	force mass
Load sell - Input resistance - nominal	385 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Isolation resistance - [Min]	2000 ΜΩ
Load cell - Recommended exitation voltage [Min]	5 V
Load cell - Recommended exitation voltage [Max]	10 V
Load cell - Input resistance - variance	3 Ω
Load cell - Output resistance - variance	3 Ω
Measuring range force [Max] (N)	50 N
Directions of force	tension compression

Approval	
CE mark	✓

Construction		
Design	"S" shaped cell	
Material	stainless steel	
Cable length	2 m	
Mounting - force application	Threaded hole M4	
Mounting - force dissipation	Threaded hole M4	

Environmental conditions	
Use temperature [Min]	-30 °C
Use temperature [Max]	70 °C

IP65

IP protection - complete device

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	150×105×40 mm
Net weight	0,03 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

1	Services (optional)	
	Article number for DAkkS calibration (tensile force)	963-161V
	Article number for DAkkS calibration (compressive force)	963-261V
	Article number for DAkkS calibration (tensile force/compressive force)	963-361V

Pictograms

STANDARD



OPTION

