

# KERN CS 1500-3P1

# KERN

4-wire "S" measuring cell made of nickel-plated steel for force and mass measurement



Dimension (W×D×H)	50,8×76,2×27,2 mm
Material	steel, nickel-plated
Cable length	3 m
Mounting - force application	Threaded hole M12
Mounting - force dissipation	Threaded hole M12

## Functions

IP protection - complete device	IP67
---------------------------------	------

## Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Ambient temperature [Min]	-35 °C
Ambient temperature [Max]	65 °C
Storage temperature [Min]	-40 °C
Storage temperature [Max]	70 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	185×155×60 mm
Net weight	0,658 kg
Shipping method	Parcel service
Net weight approx.	0,70 kg
Gross weight approx.	0,80 kg
Shipping weight	0,752 kg

## Services (optional)

Article number for factory calibration (tensile force)	961-164V
Article number for factory calibration (tensile force/ compressive force)	961-364V

## Pictograms

### STANDARD



### OPTION



## Category

Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CS P1

## Measuring System

Weighing capacity [Max]	1500 kg
Load cell connection	4-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,02%
Measuring applications	force mass
Load cell - Input resistance - nominal	350 Ω
Load cell - Output resistance - nominal	351 Ω
Load cell - Isolation resistance - [Min]	500 MΩ
Measuring range force [Max] (N)	15 kN
Directions of force	tension compression

## Approval

CE mark	✓
---------	---

## Construction

Design	"S" shaped cell
--------	-----------------