

KERN CT 2000-3Q1

Shear beam made from stainless steel

KERN



Construction

Design	Shear beam measuring cell
Dimension (W×D×H)	130×31,5×31,5 mm
Material	stainless steel
Cable length	5 m
Mounting - force application	Threaded hole M12
Mounting - force dissipation	2 × through hole Ø 13,5 mm

Functions

IP protection - complete device	IP68 IP69K
---------------------------------	---------------

Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Ambient temperature [Min]	-30 °C
Ambient temperature [Max]	70 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	250×155×60 mm
Net weight	1 kg
Shipping method	Parcel service
Net weight approx.	1,00 kg
Gross weight approx.	1,2 kg
Shipping weight	1,114 kg

Services (optional)

Article number for factory calibration (compressive force)	961-264V
--	----------

Pictograms

STANDARD



OPTION



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CT Q1

Measuring System

Weighing capacity [Max]	2000 kg
Load cell connection	6-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	0,001 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,017%
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Load cell - Input resistance - nominal	400 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Recommended excitation voltage [Min]	10 V
Load cell - Recommended excitation voltage [Max]	15 V
Load cell - Input resistance - variance	20 Ω
Load cell - Output resistance - variance	3 Ω
Directions of force	compression

Approval

CE mark	✓
---------	---