## KERN CS 5000-3P1



4-wire "S" measuring cell made of nickel-plated steel for force and mass measurement



Category	
Brand	Sauter
Product categoriy	Measuring cell
Product group	Load/force measuring cell
Product family	CS P1

Measuring System	
Weighing capacity [Max]	5000 kg
Load cell connection	4-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,02%
Load cell - Dead load [Min] (%)	0%
Measuring applications	force mass
Load sell - Input resistance - nominal	350 Ω
Load cell - Output resistance - nominal	351 Ω
Load cell - Isolation resistance - [Min]	500 ΜΩ
Measuring range force [Max] (N)	50 kN
Directions of force	tension compression

Approval	
CE mark	✓

Construction	
Design	"S" shaped cell
Dimension (W×D×H)	76,2×101,6×27,2 mm
Material	steel, nickel-plated
Cable length	6 m
Mounting - force application	Threaded hole M20 × 1,5
Mounting - force dissipation	Threaded hole M20 × 1,5
Functions	
IP protection - complete device	IP67
Environmental conditions	
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	205×170×60 mm
Net weight	1,36 kg
Shipping method	Parcel service
Net weight approx.	1,4 kg
Gross weight approx.	1,6 kg
Shipping weight	1,46 kg

-35 °C

65 °C

-40 °C 70 °C

Ambient temperature [Min]

Ambient temperature [Max]

Storage temperature [Min]

Storage temperature [Max]

Services (optional)	
Article number for factory calibration (tensile force)	961-165V
Article number for factory calibration (compressive force)	961-265V
Article number for factory calibration (tensile force/compressive force)	961-365V

## KERN CS 5000-3P1



4-wire "S" measuring cell made of nickel-plated steel for force and mass measurement

## Pictograms

**STANDARD** 





OPTION

