## KERN DE 35K5D



The long lasting story of success with dust and spray protected display device



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Platform scale
Product family	DE

Measuring System	
Construction type of the scale	Multi-division balance
Weighing system	Strain gauge
Weighing capacity [Max]	15000 g; 35000 g
Readability [d]	5 g; 10 g
Resolution	3.000, 3.500
Linearity	± 15 g; 30 g
Reproducibility	5 g; 10 g
Tare range	35000 g
Default unit	g
Units	kg g dwt tl (Tw) tl (HK) ozt mo lb oz ffa tol
Adjustment options	Adjusting with external weight
Recommended adjusting weight	30 kg (M1)
Possible calibration points	10 kg; 20 kg; 30 kg
Stabilization time	2,5 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	25 g; 50 g

Maximum creep (15 minutes)	40 g	
Maximum creep (30 minutes)	80 g	

Approval

Display digit height

CE mark	✓
Display	
Display type	LCD
Display screen size	87×29 mm
Display backlight	✓

25 mm

Construction	
Dimension display device (W×D×H)	225×110×55 mm
Dimension housing (W×D×H)	318×305×75 mm
Dimensions weighing platform (W×D×H)	318×308×75 mm
Material display housing	Plastics
Material weighing plate	stainless steel
Material platform	metal, lacquered
Dimensions weighing surface (W×D)	315×305 mm
Display device cable length	1,4 m
Allowed cable length display device [Max]	3 m
Load cells - number	4

Functions	
Number of keys for operation	5
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	1
Recipe/summing level	Sum A
Underfloor weighing	None
Interfaces	RS-232 standard
IP protection - display	IP65

Counting	
Smallest piece weight when piece counting - laboratory conditions	10 g
Smallest piece weight when piece counting - normal conditions	100 g
Reference quantity	5, 10, 20, 25, 50

1

## KERN DE 35K5D



The long lasting story of success with dust and spray protected display device

Counting resolution (laboratory conditions)

Battery connection

Battery operating time

3.500

Power Supply	
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	15 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	15 h
Rechargeable battery operating time - backlight off	30 h
Battery	9 V block
Battery / accumulator type	NiMH

Environmental conditions	
Humity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Plug-in terminals

12 h

1 d
515×392×136 mm
4,755 kg
Parcel service
4,8 kg
6 kg
5,55 kg

Services (optional)	
Article number for adjustment at the location of installation	961-248


Article number for DAkkS calibration 963-128

Article number for certificate of 969-517

Pictograms

conformity (verification)

## **STANDARD**



## **OPTION**

