

# KERN EHA 3000-0

# KERN

The compact all-round model with robust stainless steel weighing plate for use in laboratories, industries, and for teaching



Display	
Display type	LCD
Display screen size	75×32 mm
Display backlight	✓
Display digit height	22 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	225×160×50 mm
Dimensions weighing platform (W×D×H)	120×120×7 mm
Material housing	ABS plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	120×120 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	5
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
Tare function	manual (multi)
Counting function	✓

Counting	
Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Counting resolution (laboratory conditions)	3.000

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V, 600 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply & battery function (battery not included)
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK CH
Battery	2×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)

Category	
Brand	KERN
Product category	Laboratory balance
Product group	School balance
Product family	EHA

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	3000 g
Readability [d]	1 g
Resolution	3.000
Linearity	± 2 g
Reproducibility	3 g
Tare range	3000 g
Default unit	g

	g
	gn
Units	dwt
	ct
	oz

Adjustment options	Adjusting with external weight
Recommended adjusting weight	1 kg (M1); 3 kg (M1)
Possible calibration points	1 kg; 3 kg
Stabilization time	3 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	3 g
Maximum creep (15 minutes)	4 g
Maximum creep (30 minutes)	8 g

Approval	
CE mark	✓

# KERN EHA 3000-0



The compact all-round model with robust stainless steel weighing plate for use in laboratories, industries, and for teaching

Battery connection	Battery insert
Battery operating time	70 h

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	245×204×76 mm
Net weight	0,5 kg
Shipping method	Parcel service
Net weight approx.	0,50 kg
Gross weight approx.	0,75 kg
Shipping weight	0,8 kg

## Services (optional)

Article number for adjustment at the location of installation	961-247
Article number for DAkkS calibration	963-127
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION

