

KERN EMS 3000-2



Entry level model in the low-cost range with large weighing plate



Display

Display type	LCD
Display backlight	no
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	200×280×65 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	plastic
Dimensions weighing surface (W×D)	175×190 mm

Functions

Number of keys for operation	5
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Recipe/summing level	Rez A (Net total)

Counting

Smallest piece weight when piece counting - laboratory conditions	20 mg
Smallest piece weight when piece counting - normal conditions	200 mg
Reference quantity	5, 10, 20, 25, 50
Counting resolution (laboratory conditions)	150.000

Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	9 V, 300 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional
Battery	9 V block
Battery / accumulator type	Alkali(-Manganese)
Battery connection	9V Bloc
Battery operating time	40 h

Category

Brand	KERN
Product category	Laboratory balance
Product group	School balance
Product family	EMS

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	3000 g
Readability [d]	0,01 g
Resolution	300.000
Linearity	± 0,05 g
Reproducibility	0,02 g
Tare range	3000 g
Default unit	g

Units	g dwt ozt oz
Adjustment options	Adjusting with external weight
Recommended adjusting weight	3 kg (F2)
Possible calibration points	3 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,05 g
Maximum creep (15 minutes)	100 mg
Maximum creep (30 minutes)	200 mg

Approval

CE mark	✓
---------	---

KERN EMS 3000-2



Entry level model in the low-cost range with large weighing plate

Environmental conditions

Humidity of environment [Min]	40 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	310×234×164 mm
Net weight	1,575 kg
Shipping method	Parcel service
Net weight approx.	1,6 kg
Gross weight approx.	2,0 kg
Shipping weight	2,4 kg

Services (optional)

Article number for DAkkS calibration	963-127
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

