KERN FA 20



Mechanical force gauge for tensile and compressive force measurements with peak hold function



Category	
Brand	Sauter
Product categoriy	Force measurement
Product group	Mechanical force gauge
Product family	FA

Measuring System	
Default unit	N
Tolerance (% of [Max])	1%
Measuring range force [Max] (N)	20 N
Readability force [d] (N)	0,1 N
Directions of force	tension compression
Overload protection (% of [Max])	150%

Construction	
Dimension (W×D×H)	232×60×51 mm
Dimension housing (W×D×H)	232×59×51 mm
Dimensions completely mounted (W×D×H)	232×59×51 mm
Material housing	plastic
Load support (tensile force)	Hook
Mounting - force application	External thread M6

Peak function	✓	
Environmental conditions		
Ambient temperature [Min]	0 °C	
Ambient temperature [Max]	40 °C	
Storage temperature [Min]	-10 °C	
Storage temperature [Max]	40 °C	

Functions

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	325×190×95 mm
Net weight	0,5 kg
Shipping method	Parcel service
Net weight approx.	0,50 kg
Gross weight approx.	1,2 kg
Shipping weight	1,2 kg

Services (optional)	
Article number for factory calibration	961-3610
Article number for factory calibration (tensile force)	961-1610
Article number for factory calibration (compressive force)	961-2610
Article number for factory calibration (tensile force/compressive force)	961-3610

Pictograms

STANDARD









OPTION

