KERN FCB 12K-4



The new FCB: Checkweighing and portioning scale with up to three interfaces



Category				
Brand	KERN			
Product categoriy	Industrial scale			
Product group	Bench scale			
Product family	FCB-2024e			
Measuring System				
Construction type of the scale	Single-range balance			
Weighing system	Strain gauge			
Weighing capacity [Max]	12 kg			
Weighing capacity [Max] (ct)	60000 ct			
Readability [d]	0,0001 kg			
Resolution	120.000			
Linearity	± 0,0003 kg			
Reproducibility	0,0001 kg			
Default unit	kg			
Units	kg g gn dwt ozt ct lb oz ffa PCS %			
Adjustment options	Adjusting with external weight			
Recommended adjusting weight	12 kg (F2)			
Possible calibration points	2 kg; 5 kg; 10 kg; 12 kg			
Stabilization time	2 s			
Warm-up time	120 min			
Eccentric loading at 1/3 [Max]	0,0005 kg			

Maximum creep (15 minutes)	1 g			
Maximum creep (30 minutes)	2 g			
Loadcell type	aluminium IP65 silicone- coated			
Approval				
Approval				
CE mark	1			
Display				
Display type	LCD			
Display screen size	120×38 mm			
Display backlight	\checkmark			
Display digit height	25 mm			
Languages of the user interface	English Symbol language			
Construction				
Dimension housing (W×D×H)	322×267×91 mm			
Dimensions completely mounted (W×D×H)	325×270×105 mm			
Material display housing	Plastics			
Material housing	plastic			
Material weighing plate	stainless steel			
Dimensions weighing surface (W×D)	252×225 mm			
Transport safety lock - bolt torque	0,4 Nm			
Material load cell(s)	aluminium			
Levelling feet adjustable	1			
Functions				
Number of keys for operation	6			
	2 min			
Auto-off interval(s) in battery	1 min			
mode/rechargeable battery mode	30 min			
	60 min			
	30 sec			
Tare function	manual (multi)			
Percentage determination				
Counting function				
Tolerance weighing				
Tolerance weighing - type of signal	acoustically visual			
Function for averaging under unstable weighing conditions	1			
Recipe/summing level	Sum A			
Sum memory function	✓			
Underfloor weighing	None			

KERN FCB 12K-4



The new FCB: Checkweighing and portioning scale with up to three interfaces

Interfaces	RS-232 (optional) Ethernet (optional) Bluetooth BLE (v4.0) (optional) USB-Device (optional) KUP WiFi (optional)		
IP protection - complete device	-		
IP protection - display	no IP protection		
IP protection - load cell	IP65		

Counting

Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, free, Input
Counting resolution (laboratory conditions)	120.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz		
Input voltage device / power [Max]	5,9V, 1A		
Plug-in power supply type	Power adapter		
Supplied power supply	Power supply unit		
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH		
Plug-in power supply / adapter for countries - optional	EURO UK US CH		
Rechargeable battery optional	Rchrg. battery optional		
Rechargeable battery charging time	8 h		
Rechargeable battery operating time - backlight on	24 h		
Rechargeable battery operating time - backlight off	48 h		
Battery	4×1.5 V AA		
Battery / accumulator type	Li-Ion		
Battery operating time	20 h		
Environmental conditions			
Humity of environment [Min]	0 %		

Humity of environment [Min]	0 %
Humity of environment [Max]	80 %

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d			
Dimensions packaging (W×D×H)	395×335×200 mm			
Net weight	3,63 kg			
Shipping method	Parcel service			
Net weight approx.	3,8 kg			
Gross weight approx.	4,2 kg			
Shipping weight	5,3 kg			
Services (optional)				

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

1		• 6888. •	€ →	*	(((.	Ā	DAkkS
ET	ACCU	RS 232	USB	BT 4.0	WLAN	LAN	+3 DAYS