KERN FFN 1K-4N



All-round bench scale, protected by stainless steel and IP65 rating



Category

Brand	KERN
Product categoriy	Industrial scale
Product group	IP protected bench scale
Product family	FFN

Measuring System

Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	1,5 kg
Readability [d]	0,0002 kg
Resolution	7.500
Linearity	± 0,0004 kg
Reproducibility	0,0002 kg
Tare range	-1,5 kg
Default unit	kg
Units	kg Ib
Adjustment options	Adjusting with external weight
Recommended adjusting weight	1,5 kg (M1)
Possible calibration points	1,5 kg
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,001 kg
Maximum creep (15 minutes)	800 mg
Maximum creep (30 minutes)	1,6 g
Loadcell type	aluminium IP65 silicone- coated

Approval	
CE mark	1
Display	
Display type	LCD
Display backlight	1
Display digit height	25 mm
Construction	
Dimension housing (W×D×H)	243×300×127 mm
Dimensions completely mounted (W×D×H)	243×300×127 mm
Material housing	stainless steel, plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	233×193 mm
Material load cell(s)	aluminium
Levelling feet adjustable	1
Functions	
	2
Number of keys for operation	3 3 min
Auto-off interval(s) in mains power	off
mode	5 min
	15 min
Tare function	manual (multi)
Underfloor weighing	None
IP protection - complete device	IP65
Power Supply	
Input voltage power supply / power [Max]	110 V - 230 V AC
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for	EURO
countries - included with the	UK
delivery	US
	CH EURO
	AUS
Plug-in power supply / adapter for	UK
countries - optional	US
	СН
Rechargeable battery charging	12 h
time	
Rechargeable battery operating time - backlight on	30 h

KERN FFN 1K-4N



All-round bench scale, protected by stainless steel and IP65 rating

Rechargeable battery operating time - backlight off	50 h
Battery	no battery
Battery / accumulator type	Pb
Battery connection	Plug-in terminals
Environmental conditions	
Humity of environment [Min]	25 %
Humity of environment [Max]	95 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	310×402×205 mm
Net weight	3,85 kg
Shipping method	Parcel service
Net weight approx.	4,0 kg
Gross weight approx.	4,6 kg
Shipping weight	5,1 kg
Services (optional)	
Article number for adjustment at the location of installation	961-247
Article number for DAkkS calibration	963-127
Article number for certificate of conformity (verification)	969-517
D: 1	
Pictograms	

STANDARD



OPTION

