KERN FXN 10K-3N



Bench scale, protected by stainless steel and protection type IP68



Brand KERN Product categoriy Industrial scale Product group IP protected bench scale Product family FXN Measuring System Single-range balance Number of weighing ranges 1 Weighing system Strain gauge Weighing capacity [Max] 15 kg
Product groupIP protected bench scaleProduct familyFXNMeasuring SystemSingle-range balanceConstruction type of the scaleSingle-range balanceNumber of weighing ranges1Weighing systemStrain gaugeWeighing capacity [Max]15 kg
Product familyFXNMeasuring SystemSingle-range balanceConstruction type of the scaleSingle-range balanceNumber of weighing ranges1Weighing systemStrain gaugeWeighing capacity [Max]15 kg
Measuring SystemConstruction type of the scaleSingle-range balanceNumber of weighing ranges1Weighing systemStrain gaugeWeighing capacity [Max]15 kg
Construction type of the scaleSingle-range balanceNumber of weighing ranges1Weighing systemStrain gaugeWeighing capacity [Max]15 kg
Number of weighing ranges1Weighing systemStrain gaugeWeighing capacity [Max]15 kg
Weighing systemStrain gaugeWeighing capacity [Max]15 kg
Weighing capacity [Max] 15 kg
Readability [d] 0,002 kg
Resolution 7.500
Linearity ± 0,004 kg
Reproducibility 0,002 kg
Tare range -15 kg
Default unit kg
kg Units Ib PCS
Adjustment options Adjusting with external weight
Recommended adjusting weight 15 kg (M1)
Possible calibration points 15 kg
Stabilization time 2 s
Warm-up time 30 min
Eccentric loading at 1/3 [Max] 0,006 kg
Maximum creep (15 minutes) 8 g
Maximum creep (30 minutes) 16 g
Loadcell type 628HZ-0.4

Approval	
CE mark	1
Display	
Display type	LCD
Display backlight	\checkmark
Display digit height	25 mm
Construction	
Dimension housing (W×D×H)	240×280×120 mm
Dimensions completely mounted (W×D×H)	240×280×120 mm
Material housing	stainless steel, plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	236×197 mm
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	1
Functions	
Number of keys for operation	5
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min 6 min 8 min off 4 min 5 min 2 min 2 min 7 min 9 min
Tare function	manual (multi)
Counting function	\checkmark
Tolerance weighing	1
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
IP protection - complete device	IP68
Counting	
Smallest piece weight when piece counting - laboratory conditions	2 g
Smallest piece weight when piece counting - normal conditions	20 g
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	7.500

KERN FXN 10K-3N



Bench scale, protected by stainless steel and protection type IP68

Power Supply	
Supplied power supply	Battery
Battery	4×1.5 V Size D
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Battery insert
Battery voltage	6 V
Battery operating time	200 h
Battery operating time - backlight on	200 h
Battery operating time - backlight off	400 h

Environmental conditions

Humity of environment [Min]	25 %
Humity of environment [Max]	95 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	325×365×225 mm
Net weight	3,16 kg
Shipping method	Parcel service
Net weight approx.	3,2 kg
Gross weight approx.	3,8 kg
Shipping weight	5,3 kg

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

