

KERN FXN 30K-2M



Bench scale, protected by stainless steel and protection type IP68, verification optional



Approval

CE mark	✓
Pattern approval for conformity assessment	✓
Accuracy classe	III
Verification scale interval [e]	0,01 kg
Conformity assessment possible ex works	✓

Display

Display type	LCD
Display backlight	✓
Display digit height	25 mm

Construction

Dimension housing (W×D×H)	240×280×120 mm
Dimensions completely mounted (W×D×H)	240×280×120 mm
Material housing	stainless steel, plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	236×195 mm
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓

Functions

Number of keys for operation	5
	3 min
	6 min
	8 min
	off
Auto-off interval(s) in battery mode/rechargeable battery mode	4 min
	5 min
	2 min
	1 min
	7 min
	9 min
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
IP protection - complete device	IP68

Category

Brand	KERN
Product category	Industrial scale
Product group	IP protected bench scale
Product family	FXN

Measuring System

Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	30 kg
Readability [d]	0,01 kg
Resolution	3.000
Linearity	± 0,01 kg
Reproducibility	0,01 kg
Tare range	30 kg
Default unit	g
Units	kg g
Units (if device is conformity assessed)	g
Minimum weight [Min]	0,2 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	30 kg (M1)
Possible calibration points	15 kg
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,01 kg
Loadcell type	ZEMIC L6D (C3)

KERN FXN 30K-2M



Bench scale, protected by stainless steel and protection type IP68, verification optional

Counting

Smallest piece weight when piece counting - laboratory conditions	5 g
Smallest piece weight when piece counting - normal conditions	50 g
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	6.000

Power Supply

Supplied power supply	Battery
Battery	4×1.5 V Size D
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Battery insert
Battery voltage	6 V
Battery operating time	500 h
Battery operating time - backlight on	200 h
Battery operating time - backlight off	400 h

Environmental conditions

Humidity of environment [Min]	25 %
Humidity of environment [Max]	95 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	325×365×225 mm
Net weight	3,16 kg
Shipping method	Parcel service
Net weight approx.	3,2 kg
Gross weight approx.	4,4 kg
Shipping weight	5,3 kg

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

