

KERN IFB 150K20DLM



High-resolution industrial scale in heavy version, verification optional



Pattern approval for conformity assessment	✓
Accuracy classe	III
Verification scale interval [e]	0,02 kg; 0,05 kg
Conformity assessment possible ex works	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height	52 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H)	250×160×58 mm
Dimensions weighing platform (W×D×H)	650×500×136 mm
Dimensions completely mounted (W×D×H)	810×500×820 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material platform	steel, varnished
Dimensions weighing surface (W×D)	650×500 mm
Display device cable length	3 m
Allowed cable length display device [Max]	20 m
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Wall mount	✓
Stand height	600 mm
Stand inclinable	✓

Functions	
Number of keys for operation	7
Auto-off interval(s) in mains power mode	off 5 min 15 min
Auto-off interval(s) in battery mode/rechargeable battery mode	off 5 min 15 min
Tare function	manual (single & multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual

Category	
Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IFB

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	60 kg; 150 kg
Readability [d]	0,02 kg; 0,05 kg
Resolution	3.000, 3.000
Linearity	± 0,02 kg; 0,05 kg
Reproducibility	0,02 kg; 0,05 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	0,4 kg; 1 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Stabilization time	2 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,1 kg; 0,25 kg
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	6-wire

Approval	
CE mark	✓

KERN IFB 150K20DLM



High-resolution industrial scale in heavy version, verification optional

Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Sum memory function	✓
Interfaces	RS-232 standard Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - load cell	IP65
IP protection - platform	no IP protection

Counting

Smallest piece weight when piece counting - laboratory conditions	5 g
Smallest piece weight when piece counting - normal conditions	50 g
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	30.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US EURO AUS
Plug-in power supply / adapter for countries - optional	UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	35 h
Battery	no battery
Battery / accumulator type	Pb

Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	670×1050×260 mm
Net weight	18 kg
Shipping method	Parcel service
Net weight approx.	18 kg
Gross weight approx.	22 kg
Shipping weight	36,6 kg

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

