
KERN HFD 3T-3M







Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Crane scale
Product family	HFD

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	3000 kg
Readability [d]	1 kg
Resolution	3.000
Linearity	± 1 kg
Reproducibility	1 kg
Tare range	2999 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	20 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	3000 kg (M1)
Stabilization time	2 s
Warm-up time	10 min
Eccentric/Off-centre loading is not possible	✓
Loadcell type	HS-16 5T
Load cell connection	4-wire
Tolerance (% of [Max])	0,2%
Internal measuring frequency	10 Hz

Approval	
CE mark	✓
Pattern approval for conformity assessment	/
Accuracy classe	III
Verification scale interval [e]	1 kg
Conformity assessment possible ex works	✓

Display	
Display type	LCD
Display screen size	115 x40 mm
Display backlight	LED white
Display digit height	30 mm

Construction	
Dimension display device (W×D×H)	194×160×129 mm
Dimensions housing - width (A)	194 mm
Dimensions housing - depth (B)	129 mm
Dimensions housing - height/ length (C)	160 mm
Dimensions - total height/total length (D)	457 mm
Dimensions hook/bottom - hole diameter (G)	58 mm
Dimensions - inner length (E)	413 mm
Dimensions loop/top - hole diameter (F)	58 mm
Dimensions completely mounted (W×D×H)	457×194×145 mm
Material housing	cast aluminium
Material load hook	unalloyed forged steel
Material suspension	unalloyed forged steel
Material load cell(s)	high-alloy steel
Load cells - number	1

Functions	
Number of keys for operation	5
Auto-off interval(s) in mains power mode	selectable
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 15 min
Wireless operation	✓
Capacity display	✓
Tare function	manual (single)
Standby function	✓

1

KERN **HFD 3T-3M**



Robust, high-resolution crane scale, verification optional

Range of radio module 20 m

Bluetooth BTC (v4.0) Interfaces (optional, factory)

Power Supply

Input voltage power supply / 110 V - 240 V AC

power [Max]

Input voltage device / power [Max] 12 V, 2500 mA Plug-in power supply type Power adapter

Supplied power supply Battery & Power supply

EURO

UK

CH

30 h

70 h

Plug-in power supply / adapter for countries - included with the

UK CH delivery **EURO**

Plug-in power supply / adapter for countries - optional

Rechargeable battery charging 12 h

Rechargeable battery operating

time - backlight on

Rechargeable battery operating

time - backlight off

1×12 V, Type 23 A **Battery** Li-lon

Battery / accumulator type

Battery connection Plug-in terminals Battery capacity 5.200 mAh

Environmental conditions

Humity of environment [Min] 0 % Humity of environment [Max] 80 % -10 °C Ambient temperature [Min] Ambient temperature [Max] 40 °C

Packing & Shipping

Readability force [d] (N) 1 d Dimensions packaging (W×D×H) 725×275×270 mm 10 kg Net weight Shipping method Parcel service Net weight approx. 10 kg Gross weight approx. 12 kg Shipping weight 12 kg

Services (optional)

Article number for adjustment at 961-252 the location of installation Article number for conformity 965-132H assessment Article number for DAkkS 963-132H calibration

Article number for certificate of conformity (verification)

969-517

Pictograms

STANDARD









OPTION



FACTORY



