

KERN KFA 1500V20

Weighing beams, lacquered steel

KERN



Pictograms

STANDARD



FACTORY



Category

| | |
|------------------|---------------|
| Brand | KERN |
| Product category | Component |
| Product group | Weighing beam |
| Product family | KFA-V20 |

Measuring System

| | |
|-------------------------|---------|
| Weighing capacity [Max] | 1500 kg |
| Readability [d] | 500 g |

Construction

| | |
|--------------------------------------|------------------|
| Dimensions weighing platform (W×D×H) | 1200×120×100 mm |
| Material weighing plate | steel, lacquered |
| Material platform | steel, varnished |
| Dimensions weighing surface (W×D) | 1200×120 mm |
| Cable length | 5 m |
| Material load cell(s) | steel |

Functions

| | |
|---------------------------|------|
| IP protection - load cell | IP67 |
|---------------------------|------|

Packing & Shipping

| | |
|------------------------------|-----------------|
| Readability force [d] (N) | 2 d |
| Dimensions packaging (W×D×H) | 1310×490×370 mm |
| Net weight | 37 kg |
| Shipping method | Freight |
| Net weight approx. | 38 kg |
| Gross weight approx. | 60 kg |
| Shipping weight | 58 kg |

Services (optional)

| | |
|--------------------------------------|---------|
| Article number for DAkkS calibration | 963-130 |
|--------------------------------------|---------|