


KERN KFP 1500V20SNM

KERN

Weighing bridge



Functions

IP protection - load cell IP67

Environmental conditions

Ambient temperature [Min] -10 °C

Ambient temperature [Max] 40 °C

Packing & Shipping

Readability force [d] (N) 2 d

Shipping method Freight

Dimensions packaging (W×D×H) 1050×1050×260 mm

Net weight approx. 100 kg

Gross weight approx. 125 kg

Services (optional)

Article number for conformity assessment 965-230

Article number for DAkkS calibration 963-130

Piktogramme

STANDARD



Category

Brand	KERN
Product category	Measuring Technology Components
Product group	Weighing bridges

Measuring System

Readability [d]	500 g
Weighing capacity [Max]	1500 kg
Minimum weight [Min]	10 kg
Loadcell type	nickel plated steel IP67 silicone-coated + glued on plate
Load cell connection	6-guide

Approval

Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	500 g

Construction

Dimensions weighing platform (W×D×H)	1000×1000×80 mm
Dimensions weighing surface (W×D)	1000×1000 mm
Material weighing plate	steel, lacquered
Material platform	steel, varnished
Material load cell(s)	aluminium
Cable length	5 m
Allowed cable length display device [Max]	20 m
Levelling feet adjustable	✓
Load cells - number	4