# KERN KFP 150V30SM



Platform: entirely out of stainless steel



Category	
Brand	KERN
Product categoriy	Component
Product group	Platform
Product family	KFP-V30

Measuring System	
Weighing capacity [Max]	150 kg
Readability [d]	10 g
Minimum weight [Min]	1 kg
Loadcell type	stainless steel IP67 silicone-coated
Load cell connection	6-wire
Load cell OIML class	C3

### Approval

Verification scale interval [e]	50 g
Conformity assessment possible	1
ex works	

## Construction

Dimensions weighing platform (W×D×H)	400×300×107 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	400×300 mm
Cable length	3 m
Allowed cable length display device [Max]	20 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	Stainless steels
Load cells - number	1
Levelling feet adjustable	1

Functions	
IP protection - load cell	IP67
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	800×470×230 mm
Net weight	7,2 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	11 kg
Shipping weight	17,3 kg
Services (optional)	
Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

#### Pictograms

STANDARD



#### FACTORY

