

# KERN KFP 15V30M

Platform: entirely out of stainless steel

# KERN



## Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KFP-V30

## Measuring System

Weighing capacity [Max]	15 kg
Readability [d]	1 g
Minimum weight [Min]	100 g
Loadcell type	stainless steel IP67 silicone-coated
Load cell connection	6-wire
Load cell OIML class	C3

## Approval

Verification scale interval [e]	5 g
Conformity assessment possible ex works	✓

## Construction

Dimensions weighing platform (W×D×H)	300×240×104 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	300×240 mm
Cable length	3 m
Allowed cable length display device [Max]	20 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	Stainless steels
Load cells - number	1
Levelling feet adjustable	✓

## Functions

IP protection - load cell	IP67
---------------------------	------

## Packing & Shipping


Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	700×415×230 mm
Net weight	7,9 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	10 kg
Shipping weight	13,4 kg

## Services (optional)

Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128

## Pictograms

### STANDARD



### FACTORY

