

KERN KFP 30V30M

Platform: entirely out of stainless steel

KERN



Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KFP-V30

Measuring System

Weighing capacity [Max]	30 kg
Readability [d]	2 g
Minimum weight [Min]	200 g
Loadcell type	stainless steel IP67 silicone-coated
Load cell connection	6-wire
Load cell OIML class	C3

Approval

Verification scale interval [e]	10 g
Conformity assessment possible ex works	✓

Construction

Dimensions weighing platform (W×D×H)	400×300×107 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	400×300 mm
Cable length	3 m
Allowed cable length display device [Max]	3 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	Stainless steels
Load cells - number	1
Levelling feet adjustable	✓

Functions

IP protection - load cell	IP67
---------------------------	------

Packing & Shipping


Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	800×470×240 mm
Net weight	7,2 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	10 kg
Shipping weight	18 kg

Services (optional)

Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128

Pictograms

STANDARD



FACTORY

