


# KERN KIP 600V20SM

# KERN

Weighing bridge



## Category

Brand	KERN
Product category	Measuring Technology Components
Product group	Weighing bridges

## Measuring System

Readability [d]	200 g
Weighing capacity [Max]	600 kg
Eccentric loading at 1/3 [Max]	1 kg
Minimum weight [Min]	4 kg
Reproducibility	0,2 kg
Linearity	± 0,6 kg
Weighing system	Strain gauge
Resolution	3.000
Tare range	-600 kg
Stabilization time	2 s
Warm-up time	10 min
Adjustment options	Adjusting with external weight
Recommended adjusting weight	1500 kg (M2)
Loadcell type	nickel plated steel IP67 silicone-coated + glued on plate
Load cell connection	6-guide

## Approval

CE mark	✓
Conformity assessment possible ex works	✓
Verification scale interval [e]	0,2 kg

## Display

Display type	LCD
--------------	-----

Display digit height	25 mm
Display backlight	✓
Languages of the user interface	Symbol language

## Construction

Dimensions weighing platform (W×D×H)	1000×1000×108 mm
Dimension (W×D×H)	1200×1500×108 mm
Dimensions weighing surface (W×D)	1000×1000 mm
Material	steel, lacquered
Material display housing	Plastics
Material weighing plate	steel, powder-coated
Material platform	steel, powder-coated
Material load cell(s)	steel
Wall mount	✓
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	15 m
Levelling feet adjustable	✓
Load cells - number	4

## Functions

Number of keys for operation	4
Tare function	manual (single & multi)
Underfloor weighing	None
IP protection - load cell	IP67
IP protection - platform	no IP protection

## Power Supply

Plug-in power supply type	Power adapter
Supplied plug-in power supply	Power supply & battery function (battery not included)

## Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	2 d
Shipping method	Freight
Dimensions packaging (W×D×H)	1110×1035×130 mm
Net weight approx.	130 kg

# KERN KIP 600V20SM



Weighing bridge

Gross weight approx.	150 kg
Shipping weight	148 kg

## Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130
Article number for certificate of conformity (verification)	969-517

## Piktogramme

### STANDARD

---

