


KERN KFP 600V20NM

Weighing bridge



Functions

IP protection - complete device	IP67 (load cell)
IP protection - load cell	IP67
IP protection - platform	IP67

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	2 d
Shipping method	Freight
Dimensions packaging (W×D×H)	1550×1300×260 mm
Net weight approx.	150 kg
Gross weight approx.	190 kg

Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130

Piktogramme

STANDARD



Category

Brand	KERN
Product category	Measuring Technology Components
Product group	Weighing bridges

Measuring System

Readability [d]	200 g
Weighing capacity [Max]	600 kg
Minimum weight [Min]	4 kg
Loadcell type	H8C (ZEMIC)
Load cell connection	4-guide

Approval

Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	200 g

Construction

Dimensions weighing platform (W×D×H)	1500×1250×80 mm
Dimensions weighing surface (W×D)	1500×1250 mm
Material weighing plate	steel, lacquered
Material platform	steel, varnished
Material load cell(s)	alloyed steel
Cable length	5 m
Allowed cable length display device [Max]	20 m
Levelling feet adjustable	✓
Load cells - number	4