

# KERN MAP 130K1

# KERN

Hand grip dynamometer, e.g. for rehabilitation treatment after accidents



## Category

Brand	KERN
Product category	Medical scale
Product group	Hand grip dynamometer
Product family	MAP

## Measuring System

Weighing capacity [Max]	130 kg
Readability [d]	100 g
Units	kg lb
Recommended adjusting weight	60 kg (M1)
Possible calibration points	60 kg

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD graphic
Display digit height	11 mm

## Construction

Dimensions device (W×D×H)	55×102×212 mm
---------------------------	---------------

## Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	1 min
--	-------

## Power Supply

Supplied power supply	Battery
Battery	CR2450

Battery / accumulator type	Li-Metal
Battery connection	Battery insert
Battery capacity	630 mAh
Battery voltage	3 V
Battery operating time	53 h

## Environmental conditions

Use temperature [Min]	5 °C
Use temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Packing & Shipping

Dimensions transport container (W×D×H)	350×265×85 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	367×285×100 mm
Net weight	0,336 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	1,8 kg
Shipping weight	2,1 kg

## Services (optional)

Article number for factory calibration	961-167
--	---------

## Pictograms

### STANDARD



### OPTION

