

KERN KXP 300V20M



Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65



IP protection - load cell IP65

Packing & Shipping


Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	610×750×235 mm
Net weight	32,5 kg
Shipping method	Parcel service
Net weight approx.	34 kg
Gross weight approx.	36 kg
Shipping weight	34,4 kg

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Pictograms

STANDARD



FACTORY



Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KXP

Measuring System

Weighing capacity [Max]	150 kg; 300 kg
Readability [d]	10 g
Minimum weight [Min]	1 kg; 2 kg
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	6-wire

Approval

Verification scale interval [e]	50 g; 100 g
Conformity assessment possible ex works	✓

Construction

Dimensions weighing platform (W×D×H)	650×500×135 mm
Material weighing plate	stainless steel
Material platform	steel, varnished
Dimensions weighing surface (W×D)	650×500 mm
Cable length	3 m
Allowed cable length display device [Max]	10 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓

Functions

IP protection - complete device	IP65 (load cell)
---------------------------------	------------------