

# KERN KXP 60V20M



Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65



IP protection - load cell IP65

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	630×495×210 mm
Net weight	10,9 kg
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	13 kg
Shipping weight	13,1 kg

## Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

## Pictograms

### STANDARD



### FACTORY



## Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KXP

## Measuring System

Weighing capacity [Max]	30 kg; 60 kg
Readability [d]	2 g
Minimum weight [Min]	200 g; 400 g
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	6-wire

## Approval

Verification scale interval [e]	10 g; 20 g
Conformity assessment possible ex works	✓

## Construction

Dimensions weighing platform (W×D×H)	400×300×90 mm
Material weighing plate	stainless steel
Material platform	steel, varnished
Dimensions weighing surface (W×D)	400×300 mm
Cable length	3 m
Allowed cable length display device [Max]	10 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓

## Functions

IP protection - complete device	IP65 (load cell)
---------------------------------	------------------