KERN MTA 400K-1M



Sturdy handrail scale for a secure feeling during weighing – with approval for professional medical use in medical diagnostics, verification optional



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Standing aid scale
Product family	MTA

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	300 kg; 400 kg
Readability [d]	0,1 kg; 0,2 kg
Resolution	3.000, 2.000
Linearity	± 0,1 kg; 0,2 kg
Reproducibility	0,1 kg; 0,2 kg
Tare range	-399,8 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	2 kg; 4 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	400 kg (M1)
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,1 kg; 0,2 kg

Approval	
CE mark	✓
Pattern approval for conformity assessment	✓
Accuracy classe	III

Verification scale interval [e]	0,1 kg; 0,2 kg
Conformity assessment possible ex works	1
Approval according to 93/42/EEC (med.)	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height - smallest digit	5 mm
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H)	200×55×128 mm
Dimensions weighing platform (W×D×H)	780×680×68 mm
Dimensions completely mounted (W×D×H)	780×680×1100 mm
Material display housing	Plastics
Material housing	steel, lacquered
Material weighing plate	steel, lacquered
Dimensions weighing surface (W×D)	600×600 mm
Transport safety lock - bolt torque	0,1 Nm
Transport wheels	✓
Stand height	940 mm

Functions	
Number of keys for operation	7
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min 5 min 30 min 15 min
Tare function	manual (single & multi)
Hold function	✓
Function for averaging under unstable weighing conditions	1
Function for BMI calculation	✓
Interfaces	RS-232 standard

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply & battery function (battery not included)

1

KERN MTA 400K-1M



Sturdy handrail scale for a secure feeling during weighing – with approval for professional medical use in medical diagnostics, verification optional

BL . EURO
Plug-in power supply / adapter for countries - optional UK
Rechargeable battery optional Rchrg. battery optional - intern
Rechargeable battery charging time 12 h
Rechargeable battery operating time - backlight on 20 h
Rechargeable battery operating time - backlight off 40 h
Battery 6×1.5 V AA
Battery / accumulator type Alkali(-Manganese)
Battery operating time 20 h

Environmental conditions	
Humity of environment [Min]	5 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	900×876×1375 mm
Net weight	40,02 kg
Shipping method	Freight
Net weight approx.	42 kg
Gross weight approx.	65 kg
Shipping weight	216,8 kg

Services (optional)	
Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-130
Article number for DAkkS calibration	963-130
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

