KERN MPC 250K100M



Compact personal floor scale – with approval for professional medical use in medical diagnostics, verification optional



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Personal floor scale
Product family	MPC

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	250 kg
Readability [d]	0,1 kg
Resolution	2.500
Linearity	± 0,1 kg
Reproducibility	0,1 kg
Tare range	249,9 kg
Default unit	kg
Units	kg
Minimum weight [Min]	2 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 kg (M1)
Stabilization time	3 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,1 kg

Approval	
CE mark	✓
Pattern approval for conformity assessment	1
Accuracy classe	III
Verification scale interval [e]	0,1 kg

Conformity assessment possible ex works	✓
Approval according to 93/42/EEC (med.)	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H) 200×130×60 mm
Dimensions weighing platform (W×D×H)	365×370×80 mm
Material display housing	Plastics
Material housing	steel, lacquered
Material weighing plate	plastic
Display device cable length	1,8 m
Wall mount	✓

Functions	
Number of keys for operation	6
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min 5 min 30 min 15 min
PreTare function	✓
Tare function	manual (single & multi)
Hold function	✓
Function for averaging under unstable weighing conditions	1
Function for BMI calculation	✓
Interfaces	RS-232 (optional, factory)

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply & battery function (battery not included)
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH

1

KERN MPC 250K100M



Compact personal floor scale – with approval for professional medical use in medical diagnostics, verification optional

Plug-in power supply / adapter for countries - optional	EURO UK CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	40 h
Battery	6×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Battery insert
Battery operating time	20 h

Environmental conditions	
Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

1 d
560×440×200 mm
8,4 kg
Parcel service
9 kg
11 kg
10,02 kg

Services (optional)	
Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-129
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

DAkkS ACCU +3 DAYS



