KERN MWA 300K-1PM



Wheelchair platform scale with two integrated access ramps for easy access – with approval for professional medical use in medical diagnostics, verification optional



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Wheelchair platform scale
Product family	MWA

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	300 kg
Readability [d]	0,1 kg
Resolution	3.000
Linearity	± 0,1 kg
Reproducibility	0,1 kg
Tare range	-299,9 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	2 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	300 kg (M1)
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,1 kg

Approval	
CE mark	✓
Pattern approval for conformity assessment	✓

Accuracy classe	III
Verification scale interval [e]	0,1 kg
Conformity assessment possible ex works	/
Approval according to 93/42/EEC (med.)	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height - smallest digit	5 mm
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H)	200×130×60 mm
Dimensions weighing platform (W×D×H)	995×945×40 mm
Dimensions completely mounted (W×D×H)	1180×1130×1180 mm
Material display housing	Plastics
Material housing	steel, lacquered
Material weighing plate	steel, lacquered
Dimensions weighing surface (W×D)	880×840 mm
Display device cable length	3 m
Wall mount	✓
Stand height	940 mm

Functions	
Number of keys for operation	6
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min 5 min 30 min 15 min
Tare function	manual (single & multi)
Hold function	✓
Function for averaging under unstable weighing conditions	✓
Function for BMI calculation	✓
Interfaces	RS-232 standard
IP protection - load cell	IP65

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter

1

KERN MWA 300K-1PM



Wheelchair platform scale with two integrated access ramps for easy access – with approval for professional medical use in medical diagnostics, verification optional

+3 DAYS

Supplied power supply	Power supply & battery function (battery not included)
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	40 h
Battery	6×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Battery insert
Battery operating time	20 h

Environmental conditions	
Humity of environment [Min]	5 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1255×1100×285 mm
Net weight	76 kg
Shipping method	Freight
Net weight approx.	80 kg
Gross weight approx.	90 kg
Shipping weight	90 kg

Services (optional)	
Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-129
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

STANDARD GLP RS 232 PRINTER MOVE IP 65 BATT MULTI 2 DAYS OPTION DAKKS ACCU +3 DAYS FACTORY