KERN MPE 250K100HM



High quality personal floor scale with BMI function – with approval for professional medical use in medical diagnostics, verification optional



Category

Brand	KERN
Product categoriy	Medical scale
Product group	Personal floor scale
Product family	MPE

Measuring System

Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	250 kg
Readability [d]	0,1 kg
Resolution	2.500
Linearity	± 0,1 kg
Reproducibility	0,1 kg
Tare range	249,9 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	2 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 kg (M1)
Stabilization time	3 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,1 kg
Measuring range measuring rod (cm)	90-100cm @ 0,1cm ± 0,5cm 100-205cm @ 0,1cm ± 1cm

Approval	
CE mark	1
Pattern approval for conformity assessment	1
Accuracy classe	III
Verification scale interval [e]	0,1 kg
Conformity assessment possible ex works	✓
Approval according to 93/42/EEC (med.)	\checkmark
Display	
Display type	LCD
Display backlight	1
Display digit height - smallest digit	5 mm
Display digit height	25 mm
Languages of the user interface	Symbol language
Construction	
Dimension display device (W×D×H)	200×55×128 mm
Dimensions weighing platform (W×D×H)	365×360×80 mm
Dimensions completely mounted (W×D×H)	365×570×2134 mm
Material display housing	Plastics
Material housing	steel, lacquered
Material weighing plate	plastic
Dimensions weighing surface (W×D)	365×360 mm
Transport wheels	✓
Stand height	940 mm
Functions	
Number of keys for operation	7
Auto off interval(a) in maine neuror	3 min 5 min
Auto-off interval(s) in mains power mode	30 min
mode	15 min
	3 min
Auto-off interval(s) in battery	5 min
mode/rechargeable battery mode	30 min
Tous for attac	15 min
Tare function	manual (single & multi)
Hold function	1
Function for averaging under unstable weighing conditions	\checkmark
Function for BMI calculation	1
Interfaces	RS-232 standard

KERN MPE 250K100HM



High quality personal floor scale with BMI function – with approval for professional medical use in medical diagnostics, verification optional

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply & battery function (battery not included)
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	40 h
Battery	6×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Battery insert
Battery operating time	20 h

Environmental conditions

Humity of environment [Min]	5 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	00 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	1010×290×445 mm
Net weight	11,56 kg
Shipping method	Parcel service
Net weight approx.	12 kg
Gross weight approx.	15 kg
Shipping weight	26,1 kg

Services (optional)

Article number for adjustment at 961-249 the location of installation

Article number for conformity assessment	965-129
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

III)	DAkkS
ACCU	+3 DAYS

FACTORY

