KERN MWS 300K-1LM



Stretcher scale with low overall height for easy access – with approval for medical use and optionally with verification



| Category | |
|-------------------|-----------------|
| Brand | KERN |
| Product categoriy | Medical scale |
| Product group | Stretcher Scale |
| Product family | MWS-L |

| ✓ |
|--------------------------------|
| Single-range balance |
| Strain gauge |
| 300 kg |
| 0,1 kg |
| 3.000 |
| ± 0,1 kg |
| 0,1 kg |
| kg |
| kg |
| 2 kg |
| Adjusting with external weight |
| 300 kg (M1) |
| 10 min |
| 0,1 kg |
| |

| Approval | |
|--|--------|
| CE mark | ✓ |
| Pattern approval for conformity assessment | / |
| Accuracy classe | III |
| Verification scale interval [e] | 0,1 kg |
| Conformity assessment possible ex works | / |
| Approval according to 93/42/EEC (med.) | ✓ |

| Display | |
|---------------------------------|-----------------|
| Display type | LCD |
| Display digit height | 25 mm |
| Languages of the user interface | Symbol language |

| Construction | |
|---------------------------------------|------------------|
| Dimension display device (W×D×H) | 210×110×50 mm |
| Dimension housing (W×D×H) | 1500×860×68 mm |
| Dimensions weighing platform (W×D×H) | 1500×860×68 mm |
| Dimensions completely mounted (W×D×H) | 1500×860×68 mm |
| Material display housing | Plastics |
| Material housing | steel, lacquered |
| Material weighing plate | steel, lacquered |
| Dimensions weighing surface (W×D) | 800×1200 mm |
| Cable length | 1,8 m |
| Display device cable length | 2 m |
| Levelling feet adjustable | ✓ |
| Wall mount | ✓ |
| Transport wheels | ✓ |

| Functions | |
|--|-----------------------------|
| Number of keys for operation | 20 |
| Auto-off interval(s) in battery mode/rechargeable battery mode | 3 min off 4 min 5 min 2 min |
| PreTare function | ✓ |
| Tare function | manual (multi) |
| Hold function | ✓ |
| Function for averaging under unstable weighing conditions | 1 |
| Function for BMI calculation | ✓ |
| Interfaces | RS-232 standard |

| Power Supply | |
|--|--|
| Input voltage power supply / power [Max] | 100 V - 240 V, 50 / 60 Hz |
| Input voltage device / power [Max] | 12 V, 500 mA |
| Plug-in power supply type | Power adapter |
| Supplied power supply | Power supply & battery function (battery not included) |

1

KERN MWS 300K-1LM



Stretcher scale with low overall height for easy access – with approval for medical use and optionally with verification

| Plug-in power supply / adapter for countries - included with the delivery | EURO UK CH |
|---|----------------------------------|
| Plug-in power supply / adapter for countries - optional | EURO UK US CH |
| Rechargeable battery optional | Rchrg. battery optional - intern |
| Rechargeable battery charging time | 14 h |
| Rechargeable battery operating time - backlight off | 45 h |
| Battery | 6×1.5 V AA |
| Battery / accumulator type | NiMH |
| Battery operating time | 50 h |

| Environmental conditions | |
|-----------------------------|--------|
| Humity of environment [Max] | 80 % |
| Ambient temperature [Min] | 5 °C |
| Ambient temperature [Max] | 35 °C |
| Storage temperature [Min] | -20 °C |
| Storage temperature [Max] | 60 °C |

| Packing & Shipping | |
|------------------------------|------------------|
| Readability force [d] (N) | 2 d |
| Dimensions packaging (W×D×H) | 1650×1008×123 mm |
| Net weight | 42 kg |
| Shipping method | Freight |
| Net weight approx. | 42 kg |
| Gross weight approx. | 55 kg |
| Shipping weight | 55 kg |

| Services (optional) | |
|---|---------|
| Article number for adjustment at the location of installation | 961-249 |
| Article number for conformity assessment | 965-129 |
| Article number for DAkkS calibration | 963-129 |
| Article number for certificate of conformity (verification) | 969-517 |

Pictograms

STANDARD



OPTION



FACTORY

