## KERN **MPK 200K-1P**



Personal scale with column for convenient, ergonomically-optimised operation



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Personal floor scale
Product family	MPK

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	250 kg
Readability [d]	0,1 kg
Resolution	2.500
Linearity	± 1 kg
Reproducibility	0,1 kg
Default unit	kg
Units	kg Ib
Adjustment options	Adjusting with external weight
Recommended adjusting weight	250 kg (M1)
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,5 kg

Approval	
CE mark	✓
Display	
Display type	LCD
Display digit height	28 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H)	190×73×27,5 mm
Dimension housing (W×D×H)	350×370×960 mm
Dimensions weighing platform (W×D×H)	350×350×45 mm
Dimensions completely mounted (W×D×H)	350×420×955 mm
Material display housing	Plastics
Material housing	ABS plastic
Material weighing plate	plastic
Dimensions weighing surface (W×D)	350×350 mm
Stand height	900 mm

Functions	
Auto-off interval(s) in battery mode/rechargeable battery mode	10 sec
Tare function	manual (single)
Hold function	✓

Power Supply	
Supplied power supply	Battery
Battery	4×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Battery insert
Battery voltage	6 V
Battery operating time	100 h

Environmental conditions	
Humity of environment [Min]	5 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C

1 d
445×1003×145 mm
3,8 kg
Parcel service
3,8 kg
7 kg
12,9 kg

Services (optional)	
Article number for adjustment at the location of installation	961-249

1

## KERN MPK 200K-1P



Personal scale with column for convenient, ergonomically-optimised operation

Article number for DAkkS calibration 963-129

Article number for certificate of conformity (verification)

969-517

Pictograms

**STANDARD** 









OPTION

