KERN MWS 400K100DM



Stretcher scale with low overall height for easy access – with approval for medical use and optionally with verification



Category KERN Brand Product categoriy Medical scale Product group Stretcher Scale Product family MWS-L Measuring System 1 Conformity assessment possible Construction type of the scale Multi-division balance Weighing system Strain gauge Weighing capacity [Max] 300 kg; 400 kg Readability [d] 0,1 kg; 0,2 kg 3.000, 2.000 Resolution Linearity ± 0,1 kg; 0,2 kg Reproducibility 0,1 kg; 0,2 kg Default unit kg Units kg Minimum weight [Min] 2 kg Adjusting with external Adjustment options weight Recommended adjusting weight 400 kg (M1) 10 min; 10 min Warm-up time Eccentric loading at 1/3 [Max] 0,1 kg

Approval

	CE mark	\checkmark
	Pattern approval for conformity assessment	✓
	Accuracy classe	III
	Verification scale interval [e]	0,1 kg; 0,2 kg
	Conformity assessment possible ex works	1
	Approval according to 93/42/EEC (med.)	✓

Display	
Display type	LCD
Display digit height	25 mm
Languages of the user interface	Symbol language
Construction	
Dimension display device (W×D×H)	210×110×50 mm
Dimension housing (W×D×H)	210×105×45 mm
Dimensions weighing platform (W×D×H)	1255×1060×60 mm
Dimensions completely mounted (W×D×H)	1255×1060×69 mm
Material display housing	Plastics
Material housing	steel, lacquered
Material weighing plate	steel, lacquered
Dimensions weighing surface (W×D)	1000×1000 mm
Cable length	1,8 m
Display device cable length	1,8 m
Levelling feet adjustable	1
Wall mount	\checkmark
Transport wheels	\checkmark
Functions	
Number of keys for operation	20
	3 min
Auto-off interval(s) in battery	off
mode/rechargeable battery mode	4 min 5 min
	2 min
PreTare function	1
Tare function	manual (multi)
Hold function	1
Function for averaging under unstable weighing conditions	✓
Function for BMI calculation	1
Interfaces	RS-232 standard
Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply & battery function (battery not included)

KERN MWS 400K100DM



Stretcher scale with low overall height for easy access – with approval for medical use and optionally with verification

Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	14 h
Rechargeable battery operating time - backlight off	45 h
Battery	6×1.5 V AA
Battery / accumulator type	NiMH
Battery operating time	50 h

Environmental conditions

Humity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1410×1215×260 mm
Net weight	42,2 kg
Shipping method	Freight
Net weight approx.	44 kg
Gross weight approx.	65 kg
Shipping weight	61 kg

Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-130
Article number for DAkkS calibration	963-130
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

