

# KERN ORA 5PB



Refractive index measurement for laboratories and the industry



Refractometer type	Handheld refractometer
Scale - Display type	Analogue

Functions	
IP protection - complete device	-

Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Dimensions transport container (W×D×H)	205×75×55 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	215×94×65 mm
Net weight	0,30372 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	0,40 kg
Shipping weight	0,356 kg

Services (optional)	
Article number for factory calibration	961-290

## Pictograms

### STANDARD



## Category

Brand	Optics
Product category	Refractometer
Product group	Analogue refractometer
Product family	ORA-P

## Measuring System

Measuring method	Light refraction
Area of application	Urine
Appropriate calibration liquid	0 % (distilled water)
Measurement temperature [Min] (°C)	20 °C
Measurement temperature [Max] (°C)	20 °C
Scale protein serum	✓
Readout protein serum	0,1 g/100 ml
Measuring range protein serum [Min]	2 g/100 ml
Measuring range protein serum [Max]	14 g/100 ml
Scale urine (s. g. dog)	✓
Readout urine (s. g. dog)	0,001
Measuring range urine (s. g. dog) [Min]	1,000
Measuring range urine (s. g. dog) [Max]	1,060
Scale urine (s. g. cat)	✓
Readout urine (s. g. cat)	0,001
Measuring range urine (s. g. cat) [Min]	1,000
Measuring range urine (s. g. cat) [Max]	1,060

## Construction

Dimension (W×D×H)	160×40×40 mm
-------------------	--------------