

# KERN ORA 6HB

Refractive index measurement for laboratories and the industry



## Packing & Shipping

Dimensions transport container (W×D×H)	205×75×55 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	215×94×65 mm
Net weight	0,25272 kg
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	0,35 kg
Shipping weight	0,305 kg

## Pictograms

### STANDARD



## Category

Brand	Optics
Product category	Refractometer
Product group	Analogue refractometer
Product family	ORA-H

## Measuring System

Measuring method	Light refraction
Area of application	Honey
Appropriate calibration liquid	19,6 % (clove oil)
Calibration block required	✓
Measurement temperature [Min] (°C)	20 °C
Measurement temperature [Max] (°C)	20 °C
Scale water content	✓
Readout water content	0,1 %
Measuring range water content [Min]	12 %
Measuring range water content [Max]	30 %

## Construction

Dimension (W×D×H)	168×40×40 mm
Refractometer type	Handheld refractometer
Scale - Display type	Analogue

## Functions

IP protection - complete device	-
---------------------------------	---

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C