KERN OBS 102



The school microscope – for the first steps in microscopy and for use in biology lessons



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Compound microscope
Product family	OBS-1
Approval	
CE mark	1
Construction	
Dimension (W×D×H)	130×300×310 mm
Optical system	Finite
Tube type	Monocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Lens quality	achromatic
	4×
Standard objectives	10×
	40×
Nosepiece screw-in locations	3
Eyepieces fixed	\checkmark
Contrasting methods	Bright field

Ocular

e o alai	
Ocular field width	WF
Eye point	Standard
Ocular magnifications	10 x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

Focussing

Fine drive minimum

0,0025 mm

Field of view [Min]	0,45 mm
Field of view [Max]	4,5 mm
Focusing mechanism	coaxial coarse and fine drive

Illumination

Illumination intensity transmitted light	0,5 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Illumination dimmable	Transmitted light
Aperture diaphragm	\checkmark
Filter possible	✓

Power Supply

KERN OBS 102



The school microscope – for the first steps in microscopy and for use in biology lessons

Objective

Objective Achromatic 10 x / 0,25 anti-fungus Objective Achromatic 4 x / 0,1 anti-fungus Objective Achromatic 40 x / 0,65 spring, antifungus

Pictograms

STANDARD

